



► **Motorized Focus Drive MFD** for supplementary motorization of the Z-axis

Resolution:	typical 0,002 µm Depends on the speed reduction gear ratio of the microscope's fine focus, as well as the type of controller used!
Motor:	2-phase stepper motor
Max. revolutions:	60 rev. / s
Material:	aluminium
Surface:	anodic coating, black laquered
Weight:	ca. 790 g

Order Information

MFD for Leica:

DM2000 - DM3000:	order no.: 31-54-501-0000
DM4000 - DM6000:	order no.: 31-54-500-0000
DMI3000 - DMI6000:	order no.: 31-54-500-0000

MFD for Meiji Techno:

MT 8530:	order no.: 96-54-500-0000
MT5000 / MT6000:	order no.: 96-54-500-0000

MFD for Mitutoyo:

FS-110:	order no.: 00-54-501-0000
---------	---------------------------

MFD for Motic:

BA 300:	order no.: 00-54-500-0000
---------	---------------------------

MFD for Nikon:

Epiphot 200, Epiphot 300, Optiphot, Optiphot 2, L150
Eclipse E400, E600, ME600L + D, TME200, TME300:

	order no.: 45-54-500-0000
Eclipse E200:	order no.: 45-54-501-0000
Eclipse TE2000:	order no.: 45-54-502-0000
Eclipse TS100:	order no.: 45-54-503-0000
Eclipse E600FN:	order no.: 45-54-504-0000
Eclipse LV100D, LV150, 50i, 55i, 80i:	order no.: 45-54-505-0000
Eclipse L200, L300:	order no.: 45-54-506-0000
Eclipse Ti:	order no.: 45-54-507-0000

MFD for Olympus:

BX, BX41M, CKX41, GX, IX, MX50, MX61, SZX1:	order no.: 48-54-500-0000
AX70, IX61, BX51WI (back):	order no.: 48-54-502-0000
BH2:	order no.: 48-54-501-0000
BX45:	order no.: 48-54-503-0000
BX FM, BX51WI (vorn):	order no.: 48-54-504-0000
SZX2:	order no.: 48-54-505-0000

Dimensions:

