




电话: 0755-84870203

邮箱: sales@highlightoptics.com

Low Actuator Count Deformable Mirrors

Low Actuator Count DMs

Low-actuator count DM systems are economic and versatile solutions for advanced wavefront control, coming in the




With up to 140 precisely controlled elements and low inter-actuator coupling, the *Multi-DM* system is ideal for a broad range of applications including microscopy, astronomy, retinal imaging, and laser beam shaping. This DM is available in both continuous and segmented surfaces for adaptive optics or spatial light modulator applications.

The *Multi-DM* is capable of up to 5.5 μ m stroke, 2 kHz frame rate, have sub-nm step size, and no hysteresis.

High speed electronic upgrades are available for the Multi-DM systems, in the form of the X-Driver.

Demonstrated High Order Aberration Correction



Measured Zernikes: >130 actuators with low interactuator coupling create complex Zernike modes

DM Properties

Mirror Coating: Aluminum, Gold or Protected Silver					
Window:	AR coatings available				
Hysteresis:	None				
Step size:	Sub-nm (average)				
Surface Type:	Continuous (DM), Segmented (SLM)				
Fill Factor:	>99%				
Surface Figure:<30nm RMS					

Driver Specifications

Dimensions:	9" x 7" x 2.5"				
Interface:	USB 2.0				
Input Voltage:	100-240V AC				
Resolution:	14 bit				
Frame Rate:	8 kHz*				



Specifications*	Total Actuator Count	Actuator Count Across Aperture	Stroke (µm)	Aperture (mm)	Pitch (µm)	Mechanical Response (10% - 90%)	Approximate Interactuator Coupling	Price**
Multi-C-1.5	137	13	1.5	3.6	300	<40 µs	15%	\$13,000
Multi-3.5	140	12	3.5	4.4	400	<75 µs	13%	\$20,000
Multi-3.5L	140	12	3.5	4.9	450	<75 µs	13%	\$23,000
Multi-5.5	140	12	5.5	4.95	450	<100 µs	22%	Upon Request
Multi-SLM†	140	12	1.5	3.6	300	<35 µs	0%	Upon Request

^{*}High speed driver options are available.

**Includes mirror, driver and operational software