



海纳光学


电话: 0755-84870203

邮箱: sales@highlightoptics.com


ROCK

HIGH POWER SUPERCONTINUUM LASER

- Supercontinuum lasers
- SCIENTIFIC
- HIGH-POWER



Based on high repetition rate mode-locked lasers, **ROCK** operates at tens of MHz repetition rate with short pulse durations on the order of picoseconds.



FEATURES

- From visible to NIR 410 - 2400 nm
- MHz repetition rate
- Picosecond pulse width
- Total average power up to 6 W
- Visible power up to 1200 mW
- Spatially singlemode
- Maintenance-free

APPLICATIONS

- Microscopy
- Multiphoton fluorescence
- Spectroscopy
- OCT
- Metrology
- LIDAR




LEUKOS
Make a bright future

ROCK

HIGH POWER SUPERCONTINUUM LASER

Ergonomic and functional, **ROCK** provides a high average power with stable broadband spectrum which can be easily combined with our filtering solutions to provide a convenient tunable laser. An optional pulse-picker can also be integrated in order to vary the nominal repetition rate of the laser.

— Supercontinuum lasers
— SCIENTIFIC
— HIGH-POWER



OPTICAL SPECIFICATIONS		ROCK 400	ROCK 450	ROCK 480
Spectral bandwidth	minimum	< 410 nm	< 450 nm	< 480 nm
	maximum	> 2 400 nm	> 2 400 nm	> 2 400 nm
Total average power		2, 4, 5 W	2, 4, 5 W	2, 4, 6 W
Total visible power		Up to 1200 mW		
Repetition rate		40 or 60 MHz (20 and 80 on request)		
Seed pulse width		~ 6 ps		
Power stability		< +/- 1 %		
Spatial mode		Singlemode		
Polarization state		Unpolarized		
Output		FC/APC collimator (~ 1m armored cable)		
Synchronization output		Photodiode and NIM		
Interlock connector		2-pin LEMO		
OTHER SPECIFICATIONS				
Control interface		Front panel		
Operating temperature		+15°C to +35°C non condensing		
Weight		< 9 kg		
Dimensions (LxWxh)		430x330x180 mm		
Power requirements		100-240 V, 50/60 Hz		

ADDITIONAL EQUIPMENT

Achromatic collimated output

Easy fiber coupling with Pop

Tunable filters : AOTF, monochromators, custom

OPTION

Pulse picker down to 250 kHz

Optimization of spectrum in
the NIR 1100-2400nm

LEUKOS
Make a bright future

电话: 0755-84870203

邮箱: sales@highlightoptics.com



CAUTION – VISIBLE AND INVISIBLE
LASER RADIATION AVOID EYE AND
SKIN EXPOSURE TO DIRECT OR
SCATTERED RADIATION
CLASS 4 LASER PRODUCT