


# LDI

## HIGH-PERFORMANCE LASER DIODE ILLUMINATOR

### OVERVIEW

The LDI is a multiline, solid-state laser illuminator offering up to 1000mW of output power per laser line via a multimode fiber at the price of a low power LED light engine. With feedback controlled output stability and up to a 100:1 linear dynamic range, the LDI is the ideal light source for a wide range of applications including spinning disk confocal microscopy, structured illumination microscopy, FRAP, PALM/STORM, photoactivation/ photoconversion, and spatial biology.

**The LDI offers the most cost efficient price-to-performance ratio of any laser source available on the market today.**



### APPLICATIONS

- Spinning Disk Confocal Microscopy
- Super Resolution SIM Imaging
- PALM/STORM
- Optogenetics with DLPs or Multiport Illuminator
- Photoactivation/Photoconversion/FRAP
- FRAP with SLM or Multiport Illuminator
- Spatial Biology



### FEATURES AND BENEFITS

#### HIGH OUTPUT POWER:

- Shorter exposures
- Faster imaging
- Faster activation times in optogenetics and photoactivation experiments
- Faster bleaching times in FRAP experiments

#### FEEDBACK CONTROLLED OPTICAL STABILITY:

- Quantitative imaging, ideally suited for ratiometric imaging
- More repeatable optogenetics experiments

#### UP TO 100:1 LINEAR DYNAMIC RANGE:

- Ability to turn power down when needed and maintain stability

#### 7 LASER DIODES:

- Covers most of the standard fluorescence probes

#### NO USER ALIGNMENT:

- Easy to use and maintain

# LDI-7

## HIGH-PERFORMANCE LASER DIODE ILLUMINATOR





Image: Labs of CW Peleman & M.J. Basell

### LASER LINES AVAILABLE

Laser Line (nm)	Power (mW) <i>Measured out of fiber (400 μm 0.39 NA)</i>
405	300
445	1000
470	1000
520	500
528	500
555	1000
640	400

LDI-7 Output Spectra



### SPECIFICATIONS

Source Type	Laser Diodes						
Lifetime	20,000 hrs – 2 year warranty						
Laser Line (nm)	405	445	470	520	528	555	640
Width; Max FWHM (nm)	1.8	2.2	2.2	3.8	4.0	1.6	2.0
Centroid Wavelength Range (nm) <sup>1</sup>	397–407	438–450	463–470	514–523	526–535	552–557	632–644
Continuous Wave Stability <sup>2</sup>	< 2%	< 2%	< 2%	< 2%	< 2%	< 2%	< 2%
Optical Power Min (mW) <sup>1</sup>	300	1000	1000	500	500	1000	400
Max Rise Time <sup>1</sup>	< 10 μs	< 10 μs	< 10 μs	< 10 μs	< 10 μs	< 2 ms	< 10 μs
Max On/Off Frequency (Hz) <sup>3</sup>	> 1000	> 1000	> 1000	> 1000	> 1000	100	> 1000
Output Options	optical fiber <sup>4</sup>						
Control Options	TTL (>2.3 V) Analog (0–5 V) USB–DSP (virtual COM port) – SDK available upon request						
Safety	Interlocked housing Safety interlock Key interlock IEC 60825 compliant						
Dimensions	12.5" x 9.2" x 5.75", 318mm x 234mm x 146mm						
Weight	~9 lbs						
Operating Temperature	15–30° C						
Storage Temperature	–18–50° C						
Humidity	< 80% non-condensing						
Voltage	90–220 V AC, 50–60 Hz						
Fuse	None						

1. Measured at 100% intensity, 23°C ± 2°C

2. RMSE relative to the mean power measurements, measured at 100% intensity, 23°C ± 2°C

3. Measured at 100% intensity, 50% duty cycle

4. Recommended output fiber is 400 μm, 0.39 NA bifurcated fiber



海纳光学

电话: 0755-84870203

网址: [www.highlightoptics.com](http://www.highlightoptics.com)

**DANGER - LASER RADIATION AVOID EYE OR SKIN EXPOSURE TO DIRECT OR SCATTERED RADIATION CLASS 4 LASER PRODUCT**

89 North and the 89 North logo are registered trademarks of 89 North, Inc. All specifications are subject to change.

Document Number: 01-00000001190, Rev A